

SILIT-2600LV

TECHNICAL DATA SHEET

Introduction

SILIT-2600LV is amino silicone softener and a reactive functional silicone fluid, almost no d4d5d6 meets the latest EU regulations. The product can be used in various textile finishing, such as cotton, cotton blending, It has super soft feeling, it can be emulsified into micro emulsion for softeners and macro emulsion for deepening agents and smooth.

Properties

- Appearance clear to slightly turbid fluid
- pH value 7~9
- Viscosity,25°C Approx.300-1500mPa•S
- Amine number Approx. 0.5
- Compatibility Mixed use with cationic and nonionic auxiliaries
- Content of D4 <0.1%
- Content of D5 <0.1%
- Content of D6 <0.1%

Characteristics

- **SILIT-2600LV** imparts superior softness.
- Good drapability
- Good deepening ability

Applications

1 Exhaustion process:

SILIT-2600LV 0.5~1%o.w.f. (After dilution)
(30%emulsion)

Usage :40°C~50°C×15~30m n

2 Padding process:

SILIT-2600LV 5~15g/L (After dilution)
(30%emulsion)

Usage :double-dip-double-nip

Emulsification method1 for micro emulsion

SILIT-2600LV<100% solid content> emulsified to 30% solid content micro emulsion

Add:1209 Room,2 Build, No. 1588 of Huhang Road , Shanghai City, China.

① **SILIT-2600LV**----200g

+To5 ----50g

+To7 ----50g

+ Ethylene glycol monobutyl ether ----10g; then stirring 10minutes

② +H₂O ----200g; then stirring 30minutes

③ +HAc (----8g) + H₂O (----292); then slowly add the mixture and stirring 15min

④ +H₂O ----200g; then stirring 15minutes

Ttl.: 1000g / 30% solid content

Emulsification method 2 for macro emulsion

SILIT-2600LV<100% solid content> emulsified to 30% solid content micro emulsion

① **SILIT-2600LV**----250g

+To5 ----25g

+To7 ----25g

then stirring 10minutes

② slowly add H₂O ----200g in one hour; then stirring 30minutes

③ +HAc (----3g) + H₂O (----297); then slowly add the mixture and stirring 15min

④ +H₂O ----200g; then stirring 15minutes

Ttl.: 1000g / 30% solid content macro emulsion

Package

SILIT-2600LV is available in 200kg plastic drums.

Storage and shelf-life

When stored in the original unopened packaging at a temperature of between +2°C and +40°C, **SILIT-2600LV** can be used for up to 12 months after the date of manufacture marked on the packaging (DLU). Comply with storage instructions and the expiry date marked on the packaging. Past this date, **SHANGHAI HONNEUR TECH** no longer guarantees that the product meets the sales specifications.
